


# HS 770 Chassis

As at: 02/12/10 Time:22:36



# HS 770

## Chassis

As at: 02/12/10 Time:22:36

<b>Pos.</b>	<b>Description</b>	<b>Reference</b>
01	Screw M 6x110 mm	P...481H
02	Rear housing	077.112
03	Main frame	077.111
04	Hexagon screw M 6	P...490D
05	Short seal	077.137
06	PT-screw 50x16 mm	P...516H
07	PT-screw 60x20 mm	P...516M
08	Screw M 6x140 mm	P...481I
09	Nut M 6	P...495H
10	Nut support	077.114
11	Rear floor seal	077.135
12	Stopp-nut M 10	077.130
13	Support for pushbar	077.140
14	Belt guide	077.142
15	Castor complete including Items 16-19	077.144
16	Screw M 10x75 mm	P...481J
17	Washer dm 10,5 mm	P...496T
18	Castor	077.145
19	Stopp-nut M 10	P...492Q
20	Selscrew collar complete	077.125
21	Threaded insert M 5x8 mm	P...484T
22	Hexagon screw M 10	P...491N
23	Hopper seal	077.119
24	Adjustment knob	077.120